

3M™ E-A-Rfit™ Dual-Ear Validation System

Disposable Foam Test Plugs

Disposable Foam Test Plugs	Probed Test Plug SKU	Brand Names	Crossover Product SKUs and Descriptions
E-A-Rsoft™ Yellow Neons™ (regular-sized)	393-2000-50 	- E-A-Rsoft™ Yellow Neons™ - E-A-Rsoft™ Yellow Neon™ Blasts™ - E-A-Rsoft™ SuperFit™ - Tattoo™ - Nitro™	310-1250, Yellow Neons™ Uncorded in Pillow Pak Regular Size 311-1250, Yellow Neons™ Corded in Poly Bag, Regular Size 311-1252, Yellow Neon™ Blasts™ Corded in Poly Bag, Regular Size 311-1254, SuperFit™ Corded in Poly Bag, Regular Size 311-1256, Yellow Neons™ Corded in Poly Bag, Regular Size 311-1257, Yellow Neon™ Blasts™ Corded in Poly Bag, Regular Size 311-4106, Metal Detectable Corded in Poly Bag, Regular Size 311-4109, SuperFit™ Metal Detectable Corded in Poly Bag, Reg Size 311-4110, E-A-Rsoft™ Metal Detectable AV Corded, Poly Bag, Reg Size 312-1250, Yellow Neons™ Uncorded Earplugs in Poly Bag, Reg Size 312-1252, Yellow Neon™ Blasts™ Uncorded in Poly Bag, Reg Size 312-1256, SuperFit™ Uncorded Earplugs in Poly Bag, Reg Size 391-1004, Yellow Neons™ One Touch™ Refill Reg Size 391-1010, Yellow Neon™ Blasts™ One Touch™ Dispens. Refill Reg Size 391-1254, SuperFit™ One Touch™ Refill Regular Size P1000, Nitro™ Earplugs Uncorded P1001, Nitro™ Earplugs Corded P1100, Nitro™ Tattoo™ Earplug Uncorded P1101, Nitro™ Tattoo™ Earplug Corded
E-A-Rsoft™ Yellow Neons Large	393-2014-50 	E-A-Rsoft™ Yellow Neons Large	311-1251, E-A-Rsoft™ Yellow Neons™ Large Corded in Poly bag 312-1251, E-A-Rsoft™ Yellow Neons™ Large Uncorded in Poly bag 312-1255, E-A-Rsoft™ SuperFit™ Large, Uncorded 391-1005, E-A-Rsoft™ Yellow Neons™ Large Uncorded Dispens. Refill
E-A-R™ Classic™	393-2003-50 	E-A-R™ Classic™	310-1001, Uncorded Earplugs in Pillow Pak 310-1060, Uncorded in Pillow Pak 310-1080, Corded Earplugs in Poly Bag 311-1081, Corded Earplugs in Econopack Dispenser Box 311-1101, Corded Earplugs in Poly Bag 312-1080, Uncorded Earplugs in Econopack 312-1082, Uncorded Earplugs in Econopack 312-1201, Uncorded Earplugs in Poly Bag 390-1000, Uncorded Earplugs in Value Pak 391-1001, One Touch™ Refill VP311-1101, Corded Earplugs in 5 PR-100 Pak
E-A-R™ Classic™ Small	393-2007-50 	Classic™ Small	310-1103, Uncorded Earplugs in Pillow Pak 311-1106, Corded Earplugs in Poly Bag 310-4003, Platinum™ Uncorded Earplugs, Poly Bag, 310-1009, SuperFit™ 30 Uncorded Earplugs, in Pillow Pak 312-4201, SuperFit™ 30 Corded Earplugs in Poly Bag 311-1126, SuperFit™ 30 Corded Earplugs in Poly Bag 391-1002, SuperFit™ 30 One Touch™ Refill
E-A-R™ Classic™ Plus	393-2009-50 	Classic™ Plus	310-1101, Uncorded Earplugs in Pillow Pak 311-1105, Corded Earplugs in Poly Bag 311-4101, Metal-Detectable Corded Earplugs in Poly Bag 310-1008, SuperFit™ 33 Uncorded Earplugs in Pillow Pak 311-1125, SuperFit™ 33 Corded Earplugs in Poly Bag SF-01-003, SuperFit 36
E-A-R™ Classic™ Soft	Not Available	Classic™ Soft	311-6000 and 311-6001
E-A-R™ TaperFit™ 2	393-2006-50 	TaperFit™ 2	312-1219, Uncorded, Poly Bag, Reg. 312-1223, Corded, Poly Bag, Reg.
E-A-R™ TaperFit™ 2 Large	393-2027-50 	TaperFit™ 2 Large	312-1221, TaperFit™ 2 Earplugs, Uncorded 312-1224, TaperFit™ 2 Earplugs, Corded
E-A-Rsoft™ FX™	393-2004-50 	E-A-Rsoft™ FX™	312-1260, Corded Earplugs in Poly Bag 2000 PR/Case 312-1261, Uncorded Earplugs in Poly Bag 2000 PR/Case 312-1274, Corded Earplugs in Poly Bag 1000 PR/Case






Disposable Foam Test Plugs	Probed Test Plug SKU	Brand Names	Crossover Product SKUs and Descriptions
E-A-R™ E-Z-fit™	393-2005-50 	E-A-R™ E-Z-Fit™	312-1208, Uncorded Earplugs in Poly Bag 2000 PR/Case 312-1222, Corded Earplugs in Poly Bag 2000 PR/Case
E-A-Rsoft™ Grippers	393-2021-50 	E-A-Rsoft™ Grip-pers	312-6001, E-A-Rsoft™ Grippers Corded Earplugs, in Polybag
1100	393-2010-50 	3M™ 1100 3M™ 1110	1100, Uncorded Foam Earplugs in Poly Bag 1000 PR/Case 1110, Corded Foam Earplugs in Poly Bag 500 PR/Case

Push-to-Fit Probed Test Plugs

Push-to-Fit Probed Test Plugs	Probed Test Plug SKU	Brand Names	Crossover Product SKUs and Descriptions
E-A-R™ Push-Ins™	393-2002-50 	Push-Ins™	318-1000, Uncorded Earplugs in Poly Bag 318-1001, Corded Earplugs in Poly Bag 318-1002, Uncorded Earplugs in Poly Bag 318-1003, Corded Earplugs in Poly Bag 318-1004, Uncorded Earplugs in Poly Bag 318-1005, Corded Earplugs in Poly Bag 318-3000, Metal Detectable
E-A-R™ Skull Screws™	393-2012-50 	Skull Screws™	P1300, Uncorded Earplugs in Poly Bag P1301, Corded Earplugs in Poly Bag
Push-Ins™ with Grip Rings	393-2015-50 	Push-Ins™ with Grip Rings	318-1009, Push-Ins™ with Grip Rings Corded in Poly bag 318-1008, E-A-R™ Push-Ins™ with Grip Rings Uncorded, Poly bag
No Touch™ Probed	393-2013-50 	No Touch™	P2000, Uncorded in Poly Bag P2001, Corded in Poly Bag
E-A-R™ Express™ Pod Plugs™	393-2008-50 	Express™ Pod Plugs™	321-2100, Blue Grips in Pillow Pak 321-2200, Assorted Color Grips in Pillow Pak 311-1114, Corded Blue Grips in Pillow Pak 311-1115, Corded Assorted Grips in Pillow Pak 311-1127, Corded Metal-Detectable Earplugs in Pillow Pak
Push-Ins™ SofTouch™	Not available		318-4000, 318-4001, E-A-R™ Push-Ins™ SofTouch™
Pistonz™	Not available		P1400, P1401, P1401A, Pistonz™
UltraFit™ 27	Not available		340-8001, 340-8002

Reusable Probed Test Plugs

Reusable Probed Test Plugs	Probed Test Plug SKU	Brand Names	Crossover Product SKUs and Descriptions
E-A-R™ UltraFit™ Probed	393-2001-50 	- E-A-R™ UltraFit™ - E-A-R™ Tracer™	340-4001, Uncorded Earplugs in Carrying Case 340-4002, Corded Earplugs in Carrying Case 340-4003, Uncorded Earplugs in Poly Bag 340-4004, Corded Earplugs in Poly Bag 340-4007, Metal Detectable Corded Earplugs in Poly Bag 340-4014, Corded Earplugs in Econopack 340-4036, with Cotton Cord in Poly Bag 340-4044, with Cloth Cord in Paper Envelope 340-4017, Metal Detectable Corded Earplugs in Econopack TR-01-000, Tracer™ Metal Detectable Corded Earplugs VP340-4004, Corded Earplugs in 5 PR-100 Pak UF-01-012, UltraFit 20 UF-01-015, UltraFit 14
Tri-Flange™ Probed	393-2011-50 	- Tri-Flange™ - E-A-R™ UltraFit Plus™	P3000, Vinyl Corded Earplugs in Poly Bag P3001, Cloth Corded Earplugs in Poly Bag 340-6004, UltraFit Plus™ Corded Earplugs in Poly Bag 340-6002, UltraFit Plus™ Corded Earplugs in Carrying Case

Reusable Probed Test Plugs	Probed Test Plug SKU	Brand Names	Crossover Product SKUs and Descriptions
Reusable 1260	393-2016-50 	1260	1260, Reusable Earplugs, uncorded 1270, Reusable Earplugs, corded 1271, Reusable Earplugs, corded with carry case
UltraFit™ Silicone & Pump Plus	393-2017-50 	UltraFit™ Silicone	Pump Plus 340-3002, 3M™ UltraFit™ Silicone Corded Earplugs, One Size
Pomp Millennium Small	393-2023S-50 	Pomp Millennium	3M™ Pomp Millennium Small
Pomp Millennium Med	393-2023M-50 	Pomp Millennium	3M™ Pomp Millennium Medium Not available: 1241 Reusable Earplugs
Pomp Millennium Lg	393-2023L-50 	Pomp Millennium	3M™ Pomp Millennium Large
Reusable 1290	393-2024-50 	Reusable 1290	3M™ Reusable 1290, 1291, 1292, 1293
TEP/LEP/EEP	393-2030-50 	Skull Screws™ Torque™ (regular and metal detectable)	The following products fitted with this tip: TEP-100/200, LEP-100/200, LEP-200 OR, EEP-100, EEP-100 OR
	393-2031-50 	CCC-GRM-25	The following products fitted with this tip: TEP-100/200, LEP-100/200, LEP-200 OR, EEP-100, EEP-100 OR
	393-2032-50 	UltraFit™ Small	The following products fitted with this tip: TEP-100/200, LEP-100/200, LEP-200 OR, EEP-100, EEP-100 OR
	393-2033-50 	UltraFit™ MED	The following products fitted with this tip: TEP-100/200, LEP-100/200, LEP-200 OR, EEP-100, EEP-100 OR
	393-2034-50 	UltraFit™ Large	The following products fitted with this tip: TEP-100/200, LEP-100/200, LEP-200 OR, EEP-100, EEP-100 OR
	393-2035-5 	TEP-300	TEP-300

Probed Test Cushions

Probed Test Cushions	Probed Test Cushion SKU	Brand Names	Crossover Product SKUs and Descriptions
PELTOR™ Earmuff Test Cushion A 	393-3004-2	Earmuffs: • Optime™ 105 • Optime™ III Headsets: • Twin Cup	H10A, 3M™ PELTOR™ Optime™ 105 Earmuffs, Other-the-head H10P3E, 3M™ PELTOR™ Optime™ 105 Earmuffs, Hard Hat Attached H10B, PELTOR™ Optime 105 Neckband Earmuffs H540A, PELTOR™ Optime III Over-the-head Earmuffs (Bulls Eye III) H540B, PELTOR™ Optime III Neckband Earmuffs H540P3E, PELTOR™ Optime III Hard Hat Attached Earmuffs Two-way Wired Headsets: PELTOR Twin Cup Headset, ATEX, Hard Hat attached MT72H540P3E-50
PELTOR™ Earmuffs X1/X2 Test Cushions B 	393-3001-2	Earmuffs: • X1, X2 • Optime™ 95 • Optime™ 98 • Optime™ 101 • Optime™ I • Optime™ II Headsets: • LiteCom Series • ComTac™ • WorkTunes™ • ProTac Series • CH-3	X-Series and Optime Earmuffs: X1A, PELTOR™ Over-the-Head X1B, PELTOR™ Neckband X1P3E, PELTOR™ Hard Hat-Attached X1P5E & X1P5E-OR Hard Hat-Attached X1P51E, PELTOR™ Hard Hat Attached, Wide Brim X2A, PELTOR™ Over-the-Head X2B, PELTOR™ Neckband X2P3E, PELTOR™ Hard Hat-Attached X2P5E Hard Hat-Attached H505B Welding Earmuff, Neckband H510A, PELTOR™ Optime I Over-the-head H510F, PELTOR™ Optime I Folding H510B, PELTOR™ Optime I Neckband H510P3E & P3GS, PELTOR™ Optime I Hard Hat Attached H520A, PELTOR™ Optime II Over-the-head H520F, PELTOR™ Optime II Folding H520FHV, PELTOR™ Optime II Folding H520B, PELTOR™ Optime II Neckband H520P3E & P3GS, PELTOR™ Optime II Hard Hat Attached H6B, PELTOR™ Optime 95 Neckband H6A, PELTOR™ Optime™ 95, Over-the-head H6F, PELTOR™ Optime™ 95, Folding Headband H6P3E, PELTOR™ Optime™ 95, Hard Hat Attached H7A, PELTOR™ Optime™ 101, Other-the-head H7B, PELTOR™ Optime 101 Neckband H7P3E, PELTOR™ Optime™ 101, Hard Hat Attached H9A, PELTOR™ Optime™ 98, Over-the-head H9P3E, PELTOR™ Optime™ 98, Hard Hat Attached Bull's Eye™ I Earmuff, Folding Headband LiteCom Headsets: LiteCom BRS 2-way radio, Hard hat, MT53H7P3E4600 LiteCom BRS 2-way radio, Headband, MT53H7A4600 LiteCom FRS, Hard hat, MT53H7P3E4602-NA LiteCom FRS, Headband & Neckband, MT53H7A4602-NA LiteCom Plus Yellow, Hard Hat Attach (Foam & Gel Cushions), MT73H7P3E4*10* LiteCom Plus Yellow, Headband (Foam & Gel Cushions), MT73H7A4*10* LiteCom Plus Yellow, Neckband (Foam & Gel Cushions), MT73H7B4*10* LiteCom Plus, Hard hat, MT7H7P3E4*10* LiteCom Plus, Headband, MT7H7A4*10* WST™ LiteCom Plus, Hard Hat Attach (Foam & Gel Cushions), MT73H7P3E4*10WS6* WST™ LiteCom Plus, Headband (Foam & Gel Cushions), MT73H7A4*10WS6* WST™ LiteCom Plus, M-300 VersaFlo Attached (Foam & Gel Cushions) WST™ LiteCom Plus, Neckband (Foam & Gel Cushions), MT73H7B4*10WS6* WST™ LiteCom Pro III Headset - Hard Hat, MT73H7P3E4D10* WST™ LiteCom Pro III Headset - Headband, MT73H7A4D10* WST™ LiteCom Pro III Headset - Neckband, MT73H7B4D10* WST™ LiteCom Pro III Headset IS, Hard hat, MT73H7P3E4D10*-50 WST™ LiteCom Pro III Headset IS, Headband & Neckband, MT73H7B4D10*-50 WST™ LiteCom Pro III, M-300 VersaFlo Attached (Foam Cushions) ComTac Headsets: ComTac™ XPI Folding band, Foam & Gel Cushions, MT20H682FB* ComTac™ V, Folding band Gel cushions, AS Patriot 92 ComTac™ V Folding band, Foam & Gel Cushions, MT20H682FB* ComTac™ V Neckband, Foam & Gel Cushions, MT20H682BB* ComTac™ VI w/NIB Folding band, Foam & Gel Cushions, MT20H682FB*N ComTac™ VI Neckband, Foam & Gel Cushions, MT20H682BB*N ComTac™ VII Headset, Headband, Foam & Gel Cushions, MT14H41A-300* WorkTunes™ Headsets: Alert™ FM Headband, M2RX7A2-01 Alert™ FM Hard Hat Attached, M2RX7P3E2-01 WST™ Alert™ XP Headband, MRX21A2WS6 WST™ Alert™ XP Hard Hat Attached, M2RX21P3E3WS6 WST™ Alert™ XPI, Headband, M2RX21A3WS6* WorkTunes™ Pro AM/FM Headband, HRXS221A WorkTunes™ ProAM/FM, Hard Hat Attached, HRXS221P3E WST™ ProTac XPI FLX2 Neckband, Foam or Gel, MT15H7BWS6*

Probed Test Cushions	Probed Test Cushion SKU	Brand Names	Crossover Product SKUs and Descriptions
			ProTac Headsets: ProTac III Slim Headband, MT13H220A ProTac III Slim Hard Hat Attached, MT13H220P3E ProTac III Headband, MT13H221A ProTac III Hard Hat Attached, MT13H221P3E WST [™] ProTac XPI Headband, Foam or Gel MT15H7P3EWS6 WST [™] ProTac XPI HardHat Attached, Foam or Gel, MT15H7AWS6 WST [™] ProTac XPI FLX2 Headband & Hard Hat, Foam or Gel, MT15H7P3EWS6-111 WST [™] ProTac XPI FLX2 Neckband, Foam or Gel, MT15H7BWS6-111 WST [™] ProTac XPI Neckband, Foam or Gel MT15H7BWS6 2-Way Wired Headsets: CH-3 FLX2 Headset, Headband MT74H52A-110 CH-3 FLX2 Headset, Neckband MT74H52B-110 CH-3 FLX2 Headset, Hard Hat Attached MT74H52P3E-110 CH-3 FLX2 Headset with PTT, Headband MT74H52A-111 CH-3 FLX2 Headset with PTT, Neckband MT74H52B-111 CH-3 FLX2 Headset with PTT, Hard Hat Attached MT74H52P3E-111 CH-3 FLX2 Listen Only, Headband HT52A-112 CH-3 FLX2 Listen Only, Neckband HT52B-112 CH-3 FLX2 Listen Only, Hard Hat Attached HT52P3E-112 CH-3 ATEX Listen Only, Headband, HT52A-112-50 CH-3 ATEX Listen Only, Helmet Attached, HT52P3E-112-50
PELTOR[™] Earmuffs X3 Test Cushions C	393-3003-2 	Earmuffs: • X3	X3A, PELTOR [™] Over-the-Head X3B, PELTOR [™] Neckband ¹ X3P3E, PELTOR [™] Hard Hat-Attached X3P5E Hard Hat-Attached
PELTOR[™] Earmuffs X4/X5 Test Cushions D	393-3005-2 	Earmuffs: • X4, X5 Headsets • CH-5	X4A, PELTOR [™] Over-the-Head X4B, PELTOR [™] Neckband ¹ X4P3E, PELTOR [™] Hard Hat-Attached X4P5E & X4P5E-OR, Hard Hat-Attached X4P51E, PELTOR [™] Hard Hat Attached, Wide Brim X5A, PELTOR [™] Over-the-Head X5B, PELTOR [™] Neckband ¹ X5P3E, PELTOR [™] Hard Hat-Attached X5P5E, Hard Hat-Attached CH-5, PELTOR [™] High Attenuation Headset, Over-The-Head CH-5, PELTOR [™] High Attenuation Headset, Hard Hat-Attached

Banded Hearing Protectors

Banded Hearing Protectors	Banded Hearing Protectors SKU	Brand Names	Crossover Product SKUs and Descriptions
EARcaps[™] Model 200	393-2020-50 	Banded Hearing Protector: *E-A-R Caps [™]	321-2101, E-A-R Caps [™] Model 200 Hearing Protector 321-2103, Replacement Pods for E-A-R Caps [™] Model 200

NOTES:

1) E-A-Rfit™ can only be used to fit test the specific 3M hearing protectors listed in the Crossover Product column using the corresponding test probe. E-A-Rfit™ test results are not valid for any other 3M or non-3M hearing protectors.

2) If the earmuffs are worn in conjunction with a liftable visor, the visor should be in the up position when fit testing.

* The probed test cushions for X3B, X4B and X5B neckband earmuffs do not include the looped back plate, which is needed to attach the head strap for valid fit test results. The looped plate should be temporarily removed from the test subject's regular cushions and attached to the probed cushions as shown for fit testing with the headstrap.

** Remove gray back plate from the probed test cushion when fit testing all CH-3 headsets.



Personal Safety Division

3M Center, Building 235-2W-70
St. Paul, MN 55144-1000

3M PSD products are
occupational use only.

In United States of America

Technical Service: 1-800-243-4630
Customer Service: 1-800-328-1667
3M.com/workersafety

In Canada

Technical Service: 1-800-267-4414
Customer Service: 1-800-364-3577
3M.ca/Safety

© 3M 2024. All rights reserved.
3M, E-A-Rfit, the color yellow for earplugs
and all other trademarks used herein are
trademarks of 3M Company and
affiliates. Used under license in Canada.
All other trademarks are property
of their respective owners.
Please recycle.

